

Thermo Scientific Abgene 96 Well Microplates and Deepwell Plates

Clean room manufactured to ensure repeatability and cleanliness right out of the package

Thermo Scientific™ Abgene polypropylene 96 well microplates and deepwell plates offer storage security for assays, compound libraries or storing samples for either intermediate or long term. Abgene microtiter plates are manufactured to exacting specifications in our Class 100,000 clean room ISO 9001 conditions using high quality medical grade virgin polypropylene resins, which ensure confidence in the quality and performance of the storage plates. Designed to ANSI standards these 96 well microplates and deepwell plates are compatible with a variety of automated liquid handling for high throughput workflows. The polypropylene storage plates are offered with U and V bottom wells (see Figure 1) for 96 well plate configurations, along with a wide range of volumes to accommodate most applications.

Abgene 96 well polypropylene microplates are offered with multiple sealing technologies from cap mats, adhesive seals, and heat seals along with sealing equipment that was purpose built to minimize evaporation and contamination. Abgene 96 well microplates, deepwell plates, accessories, and equipment provides a purpose built platform that maximizes performance and usability for you to build your sample assay and storage workflow.

Storage Plate Applications

- Compound Storage
- High Throughput Screening
- Genomics
- Nucleic Acids
- Cell Culture



Key Features

Class 8 Clean Room 100,000 Manufactured

Virgin Polypropylene Resin





Wide breadth of products and configurations

Benefits




- Abgene polypropylene microplates are certified DNase, RNase and human DNA free for demanding applications like molecular biology or compound storage.
- Available individually packaged
- Clean room manufactured from molding to packaging to ensure repeatability and the absence of contamination
- Excellent chemical resistance to fluids like DMSO, EtOH, IPA
- Minimize the potential for extractables and leachables
- Stable at temperatures -80°C to + 121°C
- Low binding polypropylene maximizes recovery of valuable samples
- One supplier for a wide range of applications
- ANSI compliant for critical automated liquid handling applications
- Multiple well shapes and volumes optimized for sample recovery
- Increased well volume for maximum sample stored per plate as compared to competitive products

96 Well Microplates and Deepwell Plates

96 Well Microplate



96 Well Deepwell Plate



Technical Specifications

Well Bottom (Figure 1)



U-bottom

- Ideal for easy mixing



V-conical, pyramidal bottom


- Improves sample recovery and decreases dead volume



V-spindle


- Virtually eliminates dead volume in tubes during liquid handling

Square Well




U

Square Well




V-conical

Round Well




U

Round Well



V-spindle

Round Well



V-conical

Specifications

Material

Virgin Grade Polypropylene

Contaminant Free

Abgene plates are supplied free from RNase, DNase, and human DNA

Entire production process

Entire production process from molding to final packaging is carried out in a Class 100,000 clean room under ISO 9001 guidelines

Recommended Temperature Range

-80C to +121C (autoclavable)

Sealing Options

Adhesive seals
Heat seals
Storage plate caps and cap strips
Storage plate sealing mats

Customized Barcoding Services

Barcode formats: Code 128, Code 39, Interleaved 2 of 5, with flexible human-readable code position



ALPS30 Manual Heat Sealer

Protect your samples from evaporation and contamination when performing PCR or sample storage with the Thermo Scientific ALPS30 manual heat sealer. Perfect for sealing small numbers of plates in low- to medium-throughput applications, the ALPS30 unit is small enough to keep on the bench and not take up a lot of space. Its simple, ergonomic manual operation provides quick, efficient sealing at your fingertips.

Purchasing Information for 96 Well Microplates and Deepwell Plates

Cat. No.	Color	Well Shape	Bottom	Volume	Max RCF	Case Qty	Packaging	Compatible Mat
AB-1058	Natural	Round	V-Spindle	200µL	5000 x g	100	Individual	AB-0566, AB-0566/SP, AB-0674
AB-0796	Natural	Round	U	330µL	5000 x g	100	Individual	AB-0566, AB-0566/SP, AB-0674
AB-0765	Natural	Round	V-Conical	800µL	2000 x g	50	Individual	AB-0566, AB-0566/SP, AB-0674
AB-0859	Natural	Round	V-Conical	800µL	2000 x g	50	Bulk	AB-0566, AB-0566/SP, AB-0674
AB-0564	Natural	Round	U	1200µL	2000 x g	50	Individual	AB-0566, AB-0566/SP, AB-0674
AB-1127	Natural	Square	U	1200µL	2000 x g	50	Individual	AB-0675
AB-0787	Natural	Round	U	1200µL	2000 x g	50	Bulk	AB-0566, AB-0566/SP, AB-0674
AB-0661	Natural	Square	U	2200µL	5000 x g	50	Individual	AB-0675
AB-0788	Natural	Square	U	2200µL	5000 x g	50	Bulk	AB-0675
AB-0932	Natural	Square	V-Conical	2200µL	5000 x g	50	Individual	AB-0675

Associated Sample Storage Workflow Purchasing Information

Plate Seals

Cat. No.	Description
AB-0580	Basic plate seal
AB-0718	Gas permeable
AB-1450	Crystallography


Cap Strips

AB-1179	Individual
AB-0981	8-strip

Mat Caps		Well Shape
AB-0566/SP*	Pierceable	Round
AB-0566	Pierceable	Round
AB-0674	Autoclavable	Round
AB-0675	Autoclavable	Square

Plate Sealers

AB-0400	ALPS 30 Manual Heat Sealer
AB-1443A	ALPS 50V Microplate Heat Sealer w/carrier
AB-3000	ALPS 3000 Automated Heat Sealer



Seal Up to 10 Plates Per Minute with the ALPS 3000

Quickly seal in heat with the Thermo Scientific ALPS 3000 Automated Microplate Heat Sealer. This compact sealer is designed for optimal robotic integration in high throughput labs, yet still allows for manual benchtop control.

- Top-loaded seals are easily accessible
- Seven available sealing options
- Air input allows for automatic system shutoff to eliminate product waste, system hold-ups and potential injury

*mat is slightly more rigid than AB-0566.

Find out more at thermofisher.com/samplestorage

ThermoFisher
SCIENTIFIC